

Dilution Ratio Chart

UNIVERSAL SUPER CONCENTRATE (USC 25)

Powerful Multipurpose Vessel Cleaning Fluid
Designed for Universal Use Above Deck and Below.

A QUICK GUIDE TO MIXING OUR CONCENTRATE

Step 1



Measure out
concentrate
into vessel

Step 2



Add water to
concentrate in
vessel

Step 3



Shake or mix
fluid well until
clear/opaque

Step 4



Ready to be
used for
cleaning



500ml




1000ml



5 litres



25 litres



100 litres

| Ratio | USC 25 | Water |
|--------|--------|---------|
| 3 : 1 | 150ml | 350ml |
| 4 : 1 | 125ml | 375ml |
| 6 : 1 | 83ml | 417ml |
| 30 : 1 | 17ml | 483ml |
| 40 : 1 | 12.5ml | 487.5ml |

| Ratio | USC 25 | Water |
|--------|--------|-------|
| 3 : 1 | 300ml | 700ml |
| 4 : 1 | 250ml | 750ml |
| 6 : 1 | 166ml | 834ml |
| 30 : 1 | 34ml | 966ml |
| 40 : 1 | 25ml | 975ml |

| Ratio | USC 25 | Water |
|--------|--------|--------|
| 3 : 1 | 1.5L | 3.5L |
| 4 : 1 | 1.25L | 3.75L |
| 6 : 1 | 0.83L | 4.17L |
| 30 : 1 | 0.17L | 4.83L |
| 40 : 1 | 0.125L | 4.875L |

| Ratio | USC 25 | Water |
|--------|--------|---------|
| 3 : 1 | 7.5L | 17.5L |
| 4 : 1 | 6.25L | 18.75L |
| 6 : 1 | 4.15L | 20.85L |
| 30 : 1 | 0.85L | 24.15L |
| 40 : 1 | 0.625L | 24.375L |

| Ratio | USC 25 | Water |
|--------|--------|-------|
| 3 : 1 | 30L | 70L |
| 4 : 1 | 25L | 75L |
| 6 : 1 | 16.6L | 83.4L |
| 30 : 1 | 3.4L | 96.6L |
| 40 : 1 | 2.5L | 97.5L |

Heavier contaminants require higher concentration levels.

ONE SOLUTION.
HUNDREDS OF USES.



Light Cleaning
In the galley, mess
hall & cabins
SUGGESTED 6:1



Heavy Cleaning
In the engine room,
workshops & on deck
SUGGESTED 4:1



Floor Cleaning
In the engine room,
workshops & on deck
SUGGESTED 40:1



Pressure Cleaning
Concentrate within
pressure washer
SUGGESTED 6:1



Submersion Cleaning
Mechanical parts within
fluid bath
SUGGESTED 30:1



Ultrasonic Cleaning
Within designated
cleaning machines
SUGGESTED 6:1

